


FEKO ET ZRV2.5 0.5-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Z-series, Crimp contact, 4.15 mm, silver, Direct mounting
Order No.	1893970000
Type	FEKO ET ZRV2.5 0.5-1
GTIN (EAN)	4032248508198
Qty.	500 pc(s).
Packaging	Multipack bag

FEKO ET ZRV2.5 0.5-1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3.1 mm	Depth (inches)	0.122 inch
Height	19.8 mm	Height (inches)	0.78 inch
Width	4.15 mm	Width (inches)	0.163 inch
Net weight	0.404 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	CuSn	Colour	silver
----------	------	--------	--------

System specifications

Version	Spring contact
---------	----------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Conductors for clamping (rated connection)

Type of connection	Spring contact
--------------------	----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated cross-section	2.5 mm ²	Volume resistance according to IEC 60947-7-x	1.33 mΩ
Power loss in accordance with IEC 60947-7-x	0.77 W		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	c6099607-b1cd-4fc8-8f5b-8c2defa73093

Approvals

ROHS	Conform
------	---------

FEKO ET ZRV2.5 0.5-1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN