

SCREWTY M12 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Screwty® attachment is suitable for M12 round plug-in connectors, with an outside dimension of the knurled nut of 14.5 ± 0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

| | |
|------------|--|
| Version | Cable gland tool adapter for moulded M12 lines |
| Order No. | 1900100000 |
| Type | SCREWTY M12 KO O. SD |
| GTIN (EAN) | 4032248409952 |
| Qty. | 1 pc(s). |
| Packaging | Plastic bag |

SCREWTY M12 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|------|
| Net weight | 16 g |
|------------|------|

Screwing tools

| | | | |
|-------------------|-----|------|---------|
| Connection thread | M12 | Size | 14.5 mm |
|-------------------|-----|------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000149 | ETIM 7.0 | EC000149 |
| ETIM 8.0 | EC000149 | ETIM 9.0 | EC000149 |
| ECLASS 9.0 | 21-04-50-03 | ECLASS 9.1 | 21-01-90-90 |
| ECLASS 10.0 | 21-04-50-03 | ECLASS 11.0 | 21-01-90-90 |
| ECLASS 12.0 | 21-01-90-90 | ECLASS 13.0 | 21-01-90-90 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |