

SCREWTY M8 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Screwty® attachment is suitable for M8 round plug-in connectors, with an outside dimension of the knurled nut of 10 ± 0.3 mm. The tightening torque is 0.5-0.6 Nm.

General ordering data

Version	Cable gland tool adapter for moulded M8 lines
Order No.	1900110000
Type	SCREWTY M8 KO O. SD
GTIN (EAN)	4032248409969
Qty.	1 pc(s).
Packaging	Plastic bag

SCREWTY M8 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	13 g
------------	------

Screwing tools

Connection thread	M8	Size	10 mm
-------------------	----	------	-------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN