

HDC 04A ELU 1PG13S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**IP65**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Size: 1, Protection degree: IP65 (in plugged condition), Screw mounting housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 13.5 |
| Order No. | 1900330000 |
| Type | HDC 04A ELU 1PG13S |
| GTIN (EAN) | 4032248592890 |
| Qty. | 1 pc(s). |

HDC 04A ELU 1PG13S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 27 mm | Depth (inches) | 1.063 inch |
| Height | 78 mm | Height (inches) | 3.071 inch |
| Width | 36.5 mm | Width (inches) | 1.437 inch |
| Net weight | 71 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Dimensions

| | | | |
|----------------------|-----------|---------------------|---------|
| Cable entry | w. thread | Height of housing B | 54 mm |
| Total length housing | 26.5 mm | Width housing C | 26.8 mm |

General data

| | | | |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings | No | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree | IP65 (in plugged condition) |
| Surface finish | Powder coating | Tightening torque | 0.5 Nm |

Version

| | | | |
|------------------------------|----------------------------------|--------------------------------|------------------------|
| BG | 1 | Cable entry | w. thread |
| Clamp version | Side-locking clamp | Colour (RAL) | RAL 7035 |
| Design | Standard | Design of housing | Screw mounting housing |
| Design of locking system | Side-locking clamp on lower side | Internal thread | PG 13.5 |
| Number of cable entry on top | 1 | Number of cable entry sideways | 0 |
| Size | 1 | Size of cable entries | PG 13.5 |
| Suitable for ModuPlug® | No | Tightening torque | 0.5 Nm |
| Top part/bottom part/lid | lower part | Type | Plug |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC000437 |
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ECLASS 9.0 | 27-44-02-02 | ECLASS 9.1 | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |

| | |
|---------------------|-------------------------|
| Substance | Acetone |
| Chemical resistance | Conditionally resistant |
| Substance | Drilling oil |
| Chemical resistance | Resistant |
| Substance | Diesel |
| Chemical resistance | Resistant |
| Substance | Ethyl alcohol |
| Chemical resistance | Resistant |
| Substance | Transmission oil |
| Chemical resistance | Resistant |

Creation date June 3, 2024 11:18:45 PM CEST

HDC 04A ELU 1PG13S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | |
|---------------------|-------------------------|
| Substance | Hydraulic oil |
| Chemical resistance | Resistant |
| Substance | Coolant |
| Chemical resistance | Resistant |
| Substance | Petroleum benzine |
| Chemical resistance | Resistant |
| Substance | Sweat |
| Chemical resistance | Resistant |
| Substance | Premium gasoline |
| Chemical resistance | Conditionally resistant |
| Substance | Water |
| Chemical resistance | Resistant |
| Substance | UV |
| Chemical resistance | Unstable |
| Substance | Ozone |
| Chemical resistance | Unstable |

Environmental Product Compliance

| | |
|---------------------|--|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | d447edfa-0214-4f34-b5ba-82eae491b46a |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@1ff61714 de.myview.objectmodel.impl.BlockImpl@38fb83ae de.myview.objectmodel.impl.BlockImpl@31fdcf2c de.myview.objectmodel.impl.BlockImpl@2c4bad9c de.myview.objectmodel.impl.BlockImpl@32a41b6 de.myview.objectmodel.impl.BlockImpl@67a8448e de.myview.objectmodel.impl.BlockImpl@387373f8 de.myview.objectmodel.impl.BlockImpl@49a50e27 de.myview.objectmodel.impl.BlockImpl@1853d154 de.myview.objectmodel.impl.BlockImpl@3d7a7ae4 de.myview.objectmodel.impl.BlockImpl@1eb52200 de.myview.objectmodel.impl.BlockImpl@7f00c3c7 de.myview.objectmodel.impl.BlockImpl@79df6402 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Downloads


| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Product Change Notification | 20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen |
| Technical Documentation | 1900330000_HDC_04A_ELU_1PG13G_STP_Blatt_1.pdf |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |

HDC 04A ELU 1PG13S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HDC 04A ELU 1PG13S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 04A DODL 2B0 | Version |
| Order No. | 1665740000 | HDC enclosures, Size: 1, Protection degree: IP65 (in plugged condition), Cover for lower part of housing, Side-locking clamp on lower side, Standard |
| GTIN (EAN) | 4008190422769 | |
| Qty. | 1 pc(s). | |
| Type | HDC 04A DMDL 2B0 | Version |
| Order No. | 1665750000 | HDC enclosures, Size: 1, Protection degree: IP65 (in plugged condition), Cover for lower part of housing, Side-locking clamp on lower side, Standard |
| GTIN (EAN) | 4008190422776 | |
| Qty. | 1 pc(s). | |