

**HDC 24B SLU 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**IP65**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |   |
|------------|---|
| Version    | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25 |
| Order No.  | <a href="#">1901560000</a>  |
| Type       | HDC 24B SLU 1M25G   |
| GTIN (EAN) | 4032248521395   |
| Qty.       | 1 pc(s).  |

## HDC 24B SLU 1M25G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                             |         |                            |            |
|-----------------------------|---------|----------------------------|------------|
| Height                      | 64 mm   | Height (inches)            | 2.52 inch  |
| Width                       | 76.8 mm | Width (inches)             | 3.024 inch |
| Mounting dimension - height | 45 mm   | Mounting dimension - width | 132 mm     |
| Net weight                  | 426 g   |                            |            |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Dimensions

|                      |           |                      |         |
|----------------------|-----------|----------------------|---------|
| Cable entry          | w. thread | Height of base B1    | 5 mm    |
| Height of housing B  | 64 mm     | Hole pitch length A2 | 132 mm  |
| Total length housing | 120 mm    | Width base C1        | 57.5 mm |
| Width housing C      | 43 mm     |                      |         |

## General data

|                             |                             |                       |                             |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium           |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65 (in plugged condition) |
| Surface finish              | Powder coating              |                       |                             |

## Version

|                              |                               |                                |              |
|------------------------------|-------------------------------|--------------------------------|--------------|
| BG                           | 8                             | Cable entry                    | w. thread    |
| Clamp version                | End-locking clamp             | Colour (RAL)                   | RAL 7035     |
| Design                       | Standard                      | Design of housing              | Base housing |
| Design of locking system     | End-locking clamp, lower side | Internal thread                | M 25         |
| Number of cable entry on top | 0                             | Number of cable entry sideways | 1            |
| Sealing                      | NBR                           | Size                           | 8            |
| Size of cable entries        | M 25                          | Suitable for ModuPlug®         | No           |
| Top part/bottom part/lid     | lower part                    | Type                           | Base housing |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000437    | ETIM 7.0    | EC000437    |
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ECLASS 9.0  | 27-44-02-02 | ECLASS 9.1  | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |
| ECLASS 14.0 | 27-44-02-02 |             |             |

|                     |                         |
|---------------------|-------------------------|
| Substance           | Acetone                 |
| Chemical resistance | Conditionally resistant |
| Substance           | Drilling oil            |
| Chemical resistance | Resistant               |
| Substance           | Diesel                  |
| Chemical resistance | Resistant               |
| Substance           | Ethyl alcohol           |
| Chemical resistance | Resistant               |

Creation date August 28, 2024 3:43:41 PM CEST

**HDC 24B SLU 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data**

|                     |                         |
|---------------------|-------------------------|
| Substance           | Transmission oil        |
| Chemical resistance | Resistant               |
| Substance           | Hydraulic oil           |
| Chemical resistance | Resistant               |
| Substance           | Coolant                 |
| Chemical resistance | Resistant               |
| Substance           | Petroleum benzine       |
| Chemical resistance | Resistant               |
| Substance           | Sweat                   |
| Chemical resistance | Resistant               |
| Substance           | Premium gasoline        |
| Chemical resistance | Conditionally resistant |
| Substance           | Water                   |
| Chemical resistance | Resistant               |
| Substance           | UV                      |
| Chemical resistance | Unstable                |
| Substance           | Ozone                   |
| Chemical resistance | Unstable                |

**Environmental Product Compliance**

|                                      |   |
|--------------------------------------|---|
| REACH SVHC                           | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3   |
| SCIP                                 | e98b2b24-ba23-41bf-8d19-Odda3647412f  |
| Chemical resistance                  | de.myview.objectmodel.impl.BlockImpl@1128ab7c de.myview.objectmodel.impl.BlockImpl@4ae8b389<br>de.myview.objectmodel.impl.BlockImpl@7b34e436 de.myview.objectmodel.impl.BlockImpl@4ad83aeb<br>de.myview.objectmodel.impl.BlockImpl@1eff0b87 de.myview.objectmodel.impl.BlockImpl@1184872a<br>de.myview.objectmodel.impl.BlockImpl@4dc4c478 de.myview.objectmodel.impl.BlockImpl@4649a048<br>de.myview.objectmodel.impl.BlockImpl@200c2835 de.myview.objectmodel.impl.BlockImpl@158446c9<br>de.myview.objectmodel.impl.BlockImpl@3649ae05 de.myview.objectmodel.impl.BlockImpl@3d890364<br>de.myview.objectmodel.impl.BlockImpl@7c85d960 |
| RoHS Compliance Status               | Compliant with exemption  |
| RoHS Exemption (if applicable/known) | 6bl   |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E92202     |

## HDC 24B SLU 1M25G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification | <a href="#">20220214 Technical change to HDC housings</a><br><a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a> |
| Technical Documentation     | <a href="#">1901560000 HDC_24B_SLU_1M25G_STP_Blatt_1.pdf</a>   |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>   |

## HDC 24B SLU 1M25G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 24B TSLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662410000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4008190418939              | lower side, Standard, Size of cable entries: PG 29   |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TSLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662470000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4008190418991              | lower side, high, Size of cable entries: PG 21   |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TSLU 1M32G         | Version  |
| Order No.  | <a href="#">1787790000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248205233              | lower side, Standard, Size of cable entries: M 32  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TSLU 1M40G         | Version  |
| Order No.  | <a href="#">1804610000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248267538              | lower side, high, Size of cable entries: M 40  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TSLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662490000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4008190419011              | lower side, high, Size of cable entries: PG 29   |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TSLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662390000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4008190418915              | lower side, Standard, Size of cable entries: PG 21   |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TSLU 1M32G         | Version  |
| Order No.  | <a href="#">1786810000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248204052              | lower side, high, Size of cable entries: M 32  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TSLU 1M25G         | Version  |
| Order No.  | <a href="#">1787800000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248205240              | lower side, Standard, Size of cable entries: M 25  |
| Qty.       | 1 pc(s).                   |  |

## HDC 24B SLU 1M25G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 64D TOLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662610000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 21     |
| GTIN (EAN) | 4008190419134              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TOLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662630000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 29     |
| GTIN (EAN) | 4008190419158              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TOLU 1M32G         | Version  |
| Order No.  | <a href="#">1787850000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 32  |
| GTIN (EAN) | 4032248205295              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TOLU 1M25G         | Version  |
| Order No.  | <a href="#">1786870000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 25      |
| GTIN (EAN) | 4032248204113              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TOLU 1PG29G        | Version  |
| Order No.  | <a href="#">1662550000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 29 |
| GTIN (EAN) | 4008190419073              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TOLU 1M40G         | Version  |
| Order No.  | <a href="#">1983470000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 40      |
| GTIN (EAN) | 4032248687916              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 24B TOLU 1PG21G        | Version  |
| Order No.  | <a href="#">1662540000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190419066              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 64D TOLU 1M32G         | Version  |
| Order No.  | <a href="#">1786860000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 32      |
| GTIN (EAN) | 4032248204106              |  |
| Qty.       | 1 pc(s).                   |  |

## HDC 24B SLU 1M25G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 24B TOLU 1M25G         | Version   |
| Order No.  | <a href="#">1787860000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248205301              | lower side, Standard, Size of cable entries: M 25   |
| Qty.       | 1 pc(s).                   |   |

## XXL plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 64D TSLU 1M50G         | Version  |
| Order No.  | <a href="#">1111150000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248100118              | lower side, Standard, Size of cable entries: M 50  |
| Qty.       | 1 pc(s).                   |  |

**HDC 24B SLU 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****XXL plug housing, cable entry on top**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | HDC 64D TOLU 1M50G         | Version   |
| Order No.  | <a href="#">1111170000</a> | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, |
| GTIN (EAN) | 4032248100125              | lower side, Standard, Size of cable entries: M 50   |
| Qty.       | 1 pc(s).                   |   |