

HDC 40D SLU 1M32G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**IP65**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, Size of cable entries: M 32
Order No.	1903110000
Type	HDC 40D SLU 1M32G
GTIN (EAN)	4032248590117
Qty.	1 pc(s).

HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	84 mm	Height (inches)	3.307 inch
Width	79.5 mm	Width (inches)	3.13 inch
Mounting dimension - height	45 mm	Mounting dimension - width	105 mm
Net weight	440 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. thread	Height of base B1	5 mm
Height of housing B	84 mm	Hole pitch length A2	105 mm
Total length housing	93.3 mm	Width base C1	56.5 mm
Width housing C	43 mm		

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating		

Version

BG	6	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Cover	without cover	Design	high
Design of housing	Base housing	Design of locking system	End-locking clamp, lower side
Internal thread	M 32	Number of cable entry on top	0
Number of cable entry sideways	1	Sealing	NBR
Size	6	Size of cable entries	M 32
Suitable for ModuPlug®	Yes	Top part/bottom part/lid	lower part
Type	Base housing		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02
ECLASS 14.0	27-44-02-02		

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol

Creation date August 28, 2024 3:56:25 PM CEST

HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant
Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-Odda3647412f
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@c7d2094 de.myview.objectmodel.impl.BlockImpl@3551649a de.myview.objectmodel.impl.BlockImpl@3969377 de.myview.objectmodel.impl.BlockImpl@450500f0 de.myview.objectmodel.impl.BlockImpl@2019f144 de.myview.objectmodel.impl.BlockImpl@1e523469 de.myview.objectmodel.impl.BlockImpl@29e811ff de.myview.objectmodel.impl.BlockImpl@448786b2 de.myview.objectmodel.impl.BlockImpl@2bfbdcb7 de.myview.objectmodel.impl.BlockImpl@248554dd de.myview.objectmodel.impl.BlockImpl@4d0bce5b de.myview.objectmodel.impl.BlockImpl@3541635e de.myview.objectmodel.impl.BlockImpl@40aa0f25
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6bl

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads


Engineering Data	CAD data – STEP
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 40D TSLU 1M32G	Version
Order No.	1787040000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4032248204281	lower side, high, Size of cable entries: M 32
Qty.	1 pc(s).	
Type	HDC 40D TSLU 1PG29G	Version
Order No.	1657910000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4008190410964	lower side, high, Size of cable entries: PG 29
Qty.	1 pc(s).	
Type	HDC 40D TSLU 1M25G	Version
Order No.	1787050000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4032248204298	lower side, high, Size of cable entries: M 25
Qty.	1 pc(s).	
Type	HDC 40D TSLU 1M40G	Version
Order No.	1804650000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4032248267576	lower side, high, Size of cable entries: M 40
Qty.	1 pc(s).	
Type	HDC 16B TSLU 1M32G	Version
Order No.	1804640000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4032248267569	lower side, Standard, Size of cable entries: M 32
Qty.	1 pc(s).	
Type	HDC 16B TSLU 1PG21G	Version
Order No.	1657850000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4008190410902	lower side, Standard, Size of cable entries: PG 21
Qty.	1 pc(s).	
Type	HDC 40D TSLU 1PG21G	Version
Order No.	1657890000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4008190410933	lower side, high, Size of cable entries: PG 21
Qty.	1 pc(s).	
Type	HDC 16B TSLU 1M25G	Version
Order No.	1788200000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, End-locking clamp,
GTIN (EAN)	4032248205738	lower side, Standard, Size of cable entries: M 25
Qty.	1 pc(s).	

HDC 40D SLU 1M32G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 16B TOLU 1PG21G	Version
Order No.	1657960000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4008190411015	lower side, Standard, Size of cable entries: PG 21
Qty.	1 pc(s).	
Type	HDC 40D TOLU 1M32G	Version
Order No.	1787100000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4032248204441	lower side, high, Size of cable entries: M 32
Qty.	1 pc(s).	
Type	HDC 16B TOLU 1M25G	Version
Order No.	1788230000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4032248205769	lower side, Standard, Size of cable entries: M 25
Qty.	1 pc(s).	
Type	HDC 16B TOLU 1M32G	Version
Order No.	1804630000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4032248267552	lower side, Standard, Size of cable entries: M 32
Qty.	1 pc(s).	
Type	HDC 40D TOLU 1M40G	Version
Order No.	1139680000	HDC enclosures, Size: 6, Protection degree: IP65, IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4032248959792	lower side, high, Size of cable entries: M 40
Qty.	1 pc(s).	
Type	HDC 40D TOLU 1PG29G	Version
Order No.	1658020000	HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp,
GTIN (EAN)	4008190411077	lower side, high, Size of cable entries: PG 29
Qty.	1 pc(s).	