

VG M25-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 25, 10 mm, OD min. 13 - OD max. 18 mm, Polyamide 6
Order No.	1909710000
Type	VG M25-K67
GTIN (EAN)	4032248536634
Qty.	25 pc(s).

VG M25-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	37 mm	Height (inches)	1.457 inch
Length	47 mm	Length (inches)	1.85 inch
Net weight	24 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	33 mm	Cable glands	metric
External thread	M 25	Halogen	No, Yes
Length of thread	10 mm	Material	Polyamide 6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	18 mm	Outer cable diameter, min.	13 mm
Pitch of thread	1.5 mm	Protection degree	IP67
Seal insert	NBR	Silicone	No
Standards	EN/IEC 62444	Tightening torque	3.5 Nm
Torque for cap nut, max.	8.5 Nm	Torque for cap nut, min.	7.5 Nm
Torque for connecting adapter, max.	8.5 Nm	Torque for connecting adapter, min.	7.5 Nm
Torque for lock nut, max.	8.5 Nm	Torque for lock nut, min.	7.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VG M25-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M25-PO	Version
Order No.	1777950000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 25, Polyethylene
GTIN (EAN)	4032248158218	
Qty.	50 pc(s).	

Plastic lock nuts, grey

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M25 - K GR	Version
Order No.	1772470000	SKMU PA (plastic locknut), Locknut, M 25, 6 mm, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4032248130214	
Qty.	100 pc(s).	

VG M25-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M25-NP	Version
Order No.	1736250000	GWDR NP (flat gasket - neoprene), Sealing ring, M 25, Neoprene
GTIN (EAN)	4008190956042	
Qty.	100 pc(s).	