

VG PG48-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, PG 48, 14 mm, OD min. 34 - OD max. 44 mm, Polyamide 6
Order No.	1909850000
Type	VG PG48-K67
GTIN (EAN)	4032248536771
Qty.	10 pc(s).

VG PG48-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	53.5 mm	Height (inches)	2.106 inch
Length	67.5 mm	Length (inches)	2.657 inch
Net weight	92.7 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	65 mm	Cable glands	PG
External thread	PG 48	Halogen	No, Yes
Length of thread	14 mm	Material	Polyamide 6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	44 mm	Outer cable diameter, min.	34 mm
Pitch of thread	1.59 mm	Protection degree	IP67
Seal insert	NBR	Silicone	No
Tightening torque	14 Nm	Torque for cap nut, max.	21 Nm
Torque for cap nut, min.	19 Nm	Torque for connecting adapter, max.	14.5 Nm
Torque for connecting adapter, min.	13.5 Nm	Torque for lock nut, max.	14.5 Nm
Torque for lock nut, min.	13.5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VG PG48-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG48-PO	Version
Order No.	1719530000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 48,
GTIN (EAN)	4008190352790	Polyethylene
Qty.	5 pc(s).	

Plastic lock nuts, grey

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG48-K GR	Version
Order No.	1719090000	SKMU PA (plastic locknut), Locknut, PG 48, 8 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4008190352318	GF30)
Qty.	25 pc(s).	

VG PG48-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG48-NP	Version
Order No.	1719630000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 48, Neoprene
GTIN (EAN)	4008190352899	
Qty.	5 pc(s).	