

**CLI C 3-36 SDR SG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 36 x 11 mm, To customer specification
Order No.	<a href="#">1912810000</a>
Type	CLI C 3-36 SDR SG
GTIN (EAN)	4032248542659
Qty.	100 pc(s).

## CLI C 3-36 SDR SG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	36 mm	Height (inches)	1.417 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	4.5 g		

## Temperatures

Operating temperature range	80 °C
-----------------------------	-------

## General data

Colour	To customer specification	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Operating temperature range	80 °C	Operating temperature range, max.	80 °C
Orientation of print	horizontal	Printed characters	To customer specification
Printing	Custom printing	Printing method	Ink jet technology
Type of printing	To customer specification	UL 94 flammability rating	V-0
Version	Loop	Width	11 mm

## Conductor and cable markers

Conductor O.D.	8 - 16 mm	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 70 mm <sup>2</sup>
Halogen	Yes		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Environmental Product Compliance

REACH SVHC	/
------------	---

## Approvals

ROHS	Conform
------	---------

## Downloads

Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CLI C 3-36 SDR SG**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration