

**CC 30/60 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	ClipCard, Device markers, 30 x 60 mm, Holder CC-H 30/60, white
Order No.	<a href="#">1934420000</a>
Type	CC 30/60 MC NE WS
GTIN (EAN)	4032248590964
Qty.	30 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

**CC 30/60 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	30 mm	Height (inches)	1.181 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	4.6 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Application/manufacture	Holder CC-H 30/60		
Colour	white		
Halogen	No		
Material	Polyamide 66		
Material colour according to resistance code	9		
Number of markers per combination	1 MultiCard = Device markers		
Number of markers per packaging unit	Form of supply	MultiCard	
Operating temperature range	-40... 100 °C		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Printed characters	without		
Recommended industries	Machinery		
UL 94 flammability rating	V-2		
Width	60 mm		

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

## CC 30/60 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
  
[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Technical change to MultiCard material - DE</a> <a href="#">Technical change to MultiCard material - EN</a> <a href="#">MultiCard Material modification</a> <a href="#">MultiCard Material Modifikation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CC 30/60 MC NE WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**CC 30/60 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories****General ordering data**

Type	ETO CC 30/60 TRANSPAR.	Version
Order No.	<a href="#">1934440000</a>	ClipCard, Accessories, 30 x 60 mm, Transparent
GTIN (EAN)	4032248590971	
Qty.	10 pc(s).	
Type	CC-H 30/60	Version
Order No.	<a href="#">1934430000</a>	ClipCard, Accessories, 30 x 60 mm, black
GTIN (EAN)	4032248590995	
Qty.	10 pc(s).	
Type	STR CC 30/60 TRANSPARENT	Version
Order No.	<a href="#">1934450000</a>	ClipCard, Accessories, 30 x 60 mm, Transparent
GTIN (EAN)	4032248590988	
Qty.	10 pc(s).	