

WKS 2/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

General ordering data

| | |
|------------|--|
| Version | Accessories, Cross-connection slider, x 77.3 |
| Order No. | 1936180000 |
| Type | WKS 2/10 |
| GTIN (EAN) | 4032248605910 |
| Qty. | 20 pc(s). |

Technical data**Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Depth | 16.1 mm | Depth (inches) | 0.634 inch |
| Height | 18.86 mm | Height (inches) | 0.743 inch |
| Width | 77.3 mm | Width (inches) | 3.043 inch |
| Net weight | 9.3 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|--------------|--------|--------|
| Material | Polyamide 66 | Colour | orange |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|---------|
| Installation advice | Direct mounting | Type of fixing | Plugged |
| Type of mounting | Clamped | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 7.9 mm |
|-----------------|--------|

General

| | | | |
|-----------------------------------|-----------------|-----------------|----|
| Installation advice | Direct mounting | Number of poles | 10 |
| Operating temperature range, max. | 100 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Technical data

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |