

**WKS 2/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

**General ordering data**

Version	Accessories, Cross-connection slider, x 77.3
Order No.	<a href="#">1936180000</a>
Type	WKS 2/10
GTIN (EAN)	4032248605910
Qty.	20 pc(s).

**Technical data****Dimensions and weights**

Depth	16.1 mm	Depth (inches)	0.634 inch
Height	18.86 mm	Height (inches)	0.743 inch
Width	77.3 mm	Width (inches)	3.043 inch
Net weight	9.3 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

**System specifications**

Version	Cross-connector
---------	-----------------

**Additional technical data**

Installation advice	Direct mounting	Type of fixing	Plugged
Type of mounting	Clamped		

**Dimensions**

Pitch in mm (P)	7.9 mm
-----------------	--------

**General**

Installation advice	Direct mounting	Number of poles	10
Operating temperature range, max.	100 °C		

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>