

**STB 21.6/45 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

**General ordering data**

|            |   |
|------------|---|
| Version    | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| Order No.  | <a href="#">1936270000</a>                              |
| Type       | STB 21.6/45 SW  |
| GTIN (EAN) | 4032248606009   |
| Qty.       | 50 pc(s).   |

**STB 21.6/45 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 45 mm  | Depth (inches)  | 1.772 inch |
| Height     | 6.1 mm | Height (inches) | 0.24 inch  |
| Width      | 6.1 mm | Width (inches)  | 0.24 inch  |
| Net weight | 3.34 g |                 |            |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |
|----------------------------------|--------|----------------------------------|--------|

**Material data**

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

**System specifications**

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

**Additional technical data**

|                     |                 |                |                 |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
| Type of mounting    | when screwed in |                |                 |

**Dimensions**

|               |         |              |         |
|---------------|---------|--------------|---------|
| Plug-in depth | 11.1 mm | TS 35 offset | 45.5 mm |
|---------------|---------|--------------|---------|

**General**

|                     |                 |                                   |        |
|---------------------|-----------------|-----------------------------------|--------|
| Installation advice | Direct mounting | Operating temperature range, max. | 100 °C |
|---------------------|-----------------|-----------------------------------|--------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ECLASS 9.0  | 27-14-11-92 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | dce63e23-eea1-4eaa-9071-1c98fc8fa2ea |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### STB 21.6/45 SW

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures