

**SAI-AU M12 SB 4PT100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The trend from IP 20 to IP 67, or rather from machines with cabinets to ones without, reaches its zenith in the IP 67 I/O slaves. In these Plug & Play solutions, the connection of individual conductors is avoided completely. This results in a substantial time-saving and eliminates mistakes in the connection of individual conductors. Today, IP 67 bus modules represent the most modern solution for the connection of sensors and actuators with the best cost-saving potential.

**General ordering data**

Version	SAI Active, Subbus
Order No.	<a href="#">1938710000</a>
Type	SAI-AU M12 SB 4PT100
GTIN (EAN)	4032248612697
Qty.	1 pc(s).

## SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	32 mm	Height (inches)	1.26 inch
Width	30 mm	Width (inches)	1.181 inch
Length	155 mm	Length (inches)	6.102 inch
Net weight	280 g		

## Temperatures

Storage temperature	-25 °C...85 °C	Operating temperature	0 °C...60
---------------------	----------------	-----------------------	-----------

## Connections

Connection to Subbus (SUB-IN)	1 x M8 plug 4-pole, A-coded	Connection to Subbus (SUB-OUT)	1 x M8 female 4-pole, A-coded
I/O connections	4 x M12 female, 5-pole A-coded		

## Digital inputs

Diagnosis indication	red	Input filter	configurable
----------------------	-----	--------------	--------------

## Digital outputs

Diagnosis indication	red
----------------------	-----

## General data

Certificate	CE, cULus	Earth	< 200 g
Housing main material	Pocan, PBT	Protection degree	IP67
UL 94 flammability rating	5VA		

## Supply voltage

Limits	18 V DC ... 30 V DC	Operating voltage	24 V
Reverse polarity protection	Yes		

## Classifications

ETIM 6.0	EC001601	ETIM 7.0	EC001601
ETIM 8.0	EC001601	ETIM 9.0	EC001601
ECLASS 9.0	27-24-26-05	ECLASS 9.1	27-24-26-90
ECLASS 10.0	27-24-26-05	ECLASS 11.0	27-24-26-05
ECLASS 12.0	27-24-26-05	ECLASS 13.0	27-24-26-05

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	30ca4bfe-b33c-43ed-b218-3746bc09f6a6

## SAI-AU M12 SB 4PT100

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity DE PN45</a> <a href="#">CE Declaration of Conformity - DE</a> <a href="#">UKCA Declaration of Conformity - EN</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN UR67 SAI-Aktive Universal Pro DE</a> <a href="#">MAN UR67 SAI-Aktive Universal Pro EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**SAI-AU M12 SB 4PT100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****M8**

Protective caps protect unassigned plug-in stations against external influences.

**General ordering data**

Type	SAI-SK M8	Version
Order No.	<a href="#">1802760000</a>	Protected component assemblies, Protective cap
GTIN (EAN)	4032248257379	
Qty.	50 pc(s).	

**Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	ESG 8/13.5/43.3 SAI AU	Version
Order No.	<a href="#">1912130000</a>	ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent
GTIN (EAN)	4032248541164	
Qty.	5 pc(s).	

**SAI-AU M12 SB 4PT100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****M12**

Protective caps protect unassigned plug-in stations against external influences.

**General ordering data**

Type	SAI-SK-M12-UNI 2029	Version
Order No.	<a href="#">2330260000</a>	Protected component assemblies, Protective cap
GTIN (EAN)	4032248592067	
Qty.	20 pc(s).	