

## IE-BI-SCRJ2SC-MM-C

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



FO SC inserts for plug-in connectors ver.1 / 4 / 14

### General ordering data

Version	SC insert, Bulkhead insert SCRJ to 2 SC, multi-mode
Order No.	<a href="#">1964430000</a>
Type	IE-BI-SCRJ2SC-MM-C
GTIN (EAN)	4032248649044
Qty.	10 pc(s).

**IE-BI-SCRJ2SC-MM-C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	34 mm	Depth (inches)	1.339 inch
Height	13.2 mm	Height (inches)	0.52 inch
Width	15.6 mm	Width (inches)	0.614 inch
Net weight	1.1 g		

**Temperatures**

Operating temperature	-40 °C...70 °C
-----------------------	----------------

**General data**

Colour		Configuration	Connector and flange insert for variant 1, 4 and 14 housings
	Miscellaneous		
Connection 1	SC	Connection 2	SCRJ
Description of article	Bulkhead insert SCRJ to 2 SC, multimode	Fibre type	Multimode, POF
Housing main material	PA	Insertion loss	≤ 0.4 dB
Plugging cycles	1000	Protection degree	IP67 with housing
Return loss (attenuation)	≥ 30 dB		

**General standards**

Connector standard	IEC 61754-4, IEC 61754-24
--------------------	---------------------------

**Classifications**

ETIM 6.0	EC000752	ETIM 7.0	EC000752
ETIM 8.0	EC000752	ETIM 9.0	EC000752
ECLASS 9.1	19-17-01-16	ECLASS 10.0	19-17-01-16
ECLASS 11.0	19-17-01-16	ECLASS 12.0	19-17-01-16
ECLASS 13.0	19-17-01-16	ECLASS 14.0	19-17-01-16

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">GOST Approval</a> <a href="#">PROFINET Manufacturer's Declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

Creation date November 7, 2024 12:33:12 AM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

## IE-BI-SCRJ2SC-MM-C

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing

