

**BFEL + BEMU WEW WTL 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Screws for fixing the cover profiles complete the contact protection.

**General ordering data**

Version	W-Series, Fastening element
Order No.	<a href="#">1964820000</a>
Type	BFEL + BEMU WEW WTL 35
GTIN (EAN)	4032248651467
Qty.	20 pc(s).

**BFEL + BEMU WEW WTL 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	8 mm	Depth (inches)	0.315 inch
Height	14.5 mm	Height (inches)	0.571 inch
Width	14.5 mm	Width (inches)	0.571 inch
Diameter	14.5 mm	Net weight	1.3 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Material data**

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

**Additional technical data**

Installation advice	Direct mounting
---------------------	-----------------

**Dimensions**

Diameter	14.5 mm
----------	---------

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>