

WM 3/6 5.0-8.0 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Un-detachable: WM**

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm² to 16mm². Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

| | |
|--------------------|--|
| Version | WM, Conductor and cable markers, 5 - 8 mm, 17 x 10 mm, white |
| Order No. | 2006390000 |
| Type | WM 3/6 5.0-8.0 MM WS |
| GTIN (EAN) | 4050118390469 |
| Qty. | 2,000 pc(s). |
| compatible printer | 2599430000 2599440000 |

WM 3/6 5.0-8.0 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.5 mm | Depth (inches) | 0.02 inch |
| Height | 17 mm | Height (inches) | 0.669 inch |
| Width | 10 mm | Width (inches) | 0.394 inch |
| Net weight | 0.157 g | | |

Temperatures

| | | | |
|----------------------------------|--------------|----------------------------------|-----|
| Operating temperature range | -40...150 °C | Continuous operating temp., min. | -40 |
| Continuous operating temp., max. | 150 | | |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|--------------|
| Colour | white | Halogen | No |
| Material | Polyester | Operating temperature range | -40...150 °C |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Size of labelling field | 7 x 10 mm | UL 94 flammability rating | HB |
| Version | halogen-free | Width | 10 mm |

Conductor and cable markers

| | | | |
|-------------------------------|-------------------|----------------------------------|------------------------|
| Conductor O.D. | 5 - 8 mm | Conductor O.D., max. | 8 mm |
| Conductor O.D., min. | 5 mm | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 4 mm ² | Cross-section for connected wire | 4 - 16 mm ² |
| Halogen | No | Text field height | 10 mm |
| Text field width | 7 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| Catalogues | Catalogues in PDF-format |

WM 3/6 5.0-8.0 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



WM 3/6 5.0-8.0 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |

Ink ribbons

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM 76/360 SW | Version |
| Order No. | 2005080000 | Ink ribbon |
| GTIN (EAN) | 4050118389951 | |
| Qty. | 1 pc(s). | |

WM 3/6 5.0-8.0 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | MM PLUS ROLLER 110 |
| Order No. | 2672590000 |
| GTIN (EAN) | 4050118708097 |
| Qty. | 1 pc(s). |