

**KTB GP 403020 CD S4 PE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

|            |   |
|------------|---|
| Version    | Klippon TB (Terminal Box), flange plate, straight, Height: 344 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver |
| Order No.  | <a href="#">2023480000</a>  |
| Type       | KTB GP 403020 CD S4 PE  |
| GTIN (EAN) | 4050118403992   |
| Qty.       | 1 pc(s).  |

**KTB GP 403020 CD S4 PE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 3 mm    | Depth (inches)  | 0.118 inch  |
| Height     | 344 mm  | Height (inches) | 13.543 inch |
| Width      | 167 mm  | Width (inches)  | 6.575 inch  |
| Net weight | 1,385 g |                 |             |

**General information**

|                    |                 |                       |                          |
|--------------------|-----------------|-----------------------|--------------------------|
| Gland plates       | left, right     | Material              | Stainless steel 1.4404   |
| Material thickness | 3 mm            | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Surface finish     | electropolished |                       |                          |

**General information on accessories**

|                |                        |                    |      |
|----------------|------------------------|--------------------|------|
| Material       | Stainless steel 1.4404 | Material thickness | 3 mm |
| Surface finish | electropolished        |                    |      |

**Housing earth**

|                       |         |
|-----------------------|---------|
| Flange plate earthing | M6 x 15 |
|-----------------------|---------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000211    | ETIM 7.0    | EC000211    |
| ETIM 8.0    | EC000211    | ETIM 9.0    | EC000211    |
| ECLASS 9.0  | 27-14-24-21 | ECLASS 9.1  | 27-18-92-90 |
| ECLASS 10.0 | 27-14-24-21 | ECLASS 11.0 | 27-14-24-21 |
| ECLASS 12.0 | 27-14-24-21 | ECLASS 13.0 | 27-14-24-21 |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |