

KTB GP 624520 CD S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 564 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver
Order No.	2023930000
Type	KTB GP 624520 CD S4 PE
GTIN (EAN)	4050118404319
Qty.	1 pc(s).

KTB GP 624520 CD S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	564 mm	Height (inches)	22.205 inch
Width	167 mm	Width (inches)	6.575 inch
Net weight	2,230 g		

General information

Gland plates	left, right	Material	Stainless steel 1.4404
Material thickness	3 mm	Protection class (UL)	Type 3, Type 4X, Type 12
Surface finish	electropolished		

General information on accessories

Material	Stainless steel 1.4404	Material thickness	3 mm
Surface finish	electropolished		

Housing earth

Flange plate earthing	M6 x 15
-----------------------	---------

Classifications

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ETIM 9.0	EC000211
ECLASS 9.0	27-14-24-21	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-14-24-21	ECLASS 11.0	27-14-24-21
ECLASS 12.0	27-14-24-21	ECLASS 13.0	27-14-24-21

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	