

**TST 10 SAKC10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

**General ordering data**

Version	Mounting foot for mounting rail, Polyamide 66
Order No.	<a href="#">2082460000</a>
Type	TST 10 SAKC10
GTIN (EAN)	4008190223380
Qty.	400 pc(s).

## TST 10 SAKC10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	7.4 mm	Depth (inches)	0.291 inch
Height	51 mm	Height (inches)	2.008 inch
Width	7.4 mm	Width (inches)	0.291 inch
Net weight	3.578 g		

## Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

## Material data

Material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

## System specifications

Version	For the mounting rails
---------	------------------------

## General

Operating temperature range, max.	100 °C
-----------------------------------	--------

## Classifications

ETIM 6.0	EC002625	ETIM 7.0	EC002625
ETIM 8.0	EC002625	ETIM 9.0	EC002625
ECLASS 9.0	27-18-28-07	ECLASS 9.1	23-15-90-90
ECLASS 10.0	27-18-28-07	ECLASS 11.0	27-18-28-07
ECLASS 12.0	27-18-28-07	ECLASS 13.0	27-18-28-07

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	45173c19-8a33-4947-bc2b-512a20c76dcd

## Approvals

ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--