

**SAKQB 6/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 8.00, Insu- lated: No
Order No.	<a href="#">2111230000</a>
Type	SAKQB 6/10
GTIN (EAN)	4050118440607
Qty.	10 pc(s).
Local product	Only available in certain countries

**SAKQB 6/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****General ordering data**

Local product	Only available in certain countries
---------------	-------------------------------------

**Dimensions and weights**

Depth	15 mm	Depth (inches)	0.591 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	19.74 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Additional technical data**

Type of fixing	when screwed in
----------------	-----------------

**Dimensions**

Pitch in mm (P)	8 mm
-----------------	------

**General**

Number of poles	10
-----------------	----

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>