

**PAC-HE40-F-HF-10M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

Version	
Order No.	<a href="#">2425680100</a>
Type	PAC-HE40-F-HF-10M
GTIN (EAN)	4099986593121
Qty.	1 pc(s).

**PAC-HE40-F-HF-10M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	1,491 g
------------	---------

**Temperatures**

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

**General Data**

Cable	Cable LIHH	Cable length	10 m
Connector PLC side	H0.14/10 (FERRULES 0.14mm <sup>2</sup> )	Interface connector	FLAT CABLE PLANO HE10 40P
Number of poles, min.	40-pole	Suitable for	Digital signals
Wire cross-section	0.14 mm <sup>2</sup>		

**Electrical Data**

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150 mΩ/m
Total current, max.	3 A		

**Classifications**

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--