

PAC-D37F-F-HF-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

General ordering data

Version	
Order No.	2426050030
Type	PAC-D37F-F-HF-3M
GTIN (EAN)	4099986598997
Qty.	1 pc(s).

PAC-D37F-F-HF-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	949 g
------------	-------

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

General Data

Cable length	3 m	Connector PLC side	H0.25/10 (FERRULES 0.25mm ²)
Interface connector	SUB-D FEMALE 37P	Number of poles, min.	37-pole
Suitable for	Analogue signals	Wire cross-section	0.25 mm ²

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--