

**FAD S5135 SL42 A R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

**General ordering data**

Version	
Order No.	<a href="#">2435110000</a>
Type	FAD S5135 SL42 A R
GTIN (EAN)	4050118446975
Qty.	1 pc(s).

## FAD S5135 SL42 A R

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	23 mm	Depth (inches)	0.906 inch
Height	283 mm	Height (inches)	11.142 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	127 g		

## Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

## Connection data

Connection (field side)	SL 5.08 mm
-------------------------	------------

## Ratings data

Operating voltage	250 V AC	Max. current per channel	4 A
Total operating current	32 A		

## Insulation coordination (EN50178)

Rated insulation voltage	< 250 V AC	Surge voltage category	II
Pollution severity level	2	Insulation test voltage AC	1.2 kV

## Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9d5ff7ee-74dc-449b-a1db-a29604b9b3e9

## Approvals

Approvals



ROHS

Conform

## Downloads

Catalogues [Catalogues in PDF-format](#)

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Drawings

[illegible]