

VT CL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Version	Testing tools, Cable detector
Order No.	2436660000
Type	VT CL
GTIN (EAN)	4050118450026
Qty.	1 pc(s).

VT CL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	23 mm	Depth (inches)	0.906 inch
Height	25 mm	Height (inches)	0.984 inch
Width	155 mm	Width (inches)	6.102 inch
Net weight	55.1 g		

Measuring and testing devices

Battery type	1.5 V type AAA battery	Display	Visual & acoustic
Measuring range category	CAT IV 1000 V	Protection degree	IP65
Rated voltage, max.	1000 V AC	Rated voltage, min.	90 V AC
Tested and approved according to	DIN EN 61010-1, DIN EN 61326		

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ETIM 9.0	EC000494
ECLASS 9.0	27-20-03-08	ECLASS 9.1	27-20-03-08
ECLASS 10.0	27-20-03-08	ECLASS 11.0	27-20-03-08
ECLASS 12.0	27-20-03-08	ECLASS 13.0	27-20-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

VT CL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories

Accessories for testing and measuring equipment



General ordering data

Type	BATTERIE 1,5V MICRO	Version
Order No.	9201310000	Testing tools, Battery
GTIN (EAN)	4032248421121	
Qty.	2 pc(s).	