

VT LCL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Version	Testing tools, Cable detector
Order No.	2436670000
Type	VT LCL
GTIN (EAN)	4050118450033
Qty.	1 pc(s).

VT LCL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	23 mm	Depth (inches)	0.906 inch
Height	25 mm	Height (inches)	0.984 inch
Width	155 mm	Width (inches)	6.102 inch
Net weight	55.3 g		

Technical data

Description of article	Non-contact voltage tester
------------------------	----------------------------

Measuring and testing devices

Battery type	1.5 V type AAA battery	Display	Visual & acoustic
Measuring range category	CAT IV 1000 V	Protection degree	IP65
Rated voltage, max.	1000 V AC	Rated voltage, min.	12 V AC
Tested and approved according to	DIN EN 61010-1, DIN EN 61326		

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ETIM 9.0	EC000494
ECLASS 9.0	27-20-03-08	ECLASS 9.1	27-20-03-08
ECLASS 10.0	27-20-03-08	ECLASS 11.0	27-20-03-08
ECLASS 12.0	27-20-03-08	ECLASS 13.0	27-20-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format