

**EPG 60****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Version	Pressing tools, Tools, Pressing tool, 6mm <sup>2</sup> , 300mm <sup>2</sup> , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Order No.	<a href="#">2453810000</a>
Type	EPG 60
GTIN (EAN)	4050118468434
Qty.	1 pc(s).

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	355 mm	Height (inches)	13.976 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	3,300 g		

## Technical data

Charging time	0.5 h		
Description of article	Crimping tool 6 - 300 mm <sup>2</sup>		
Operating voltage	18 V		
Pressing force	nominal	60 kN	

## Description of contact

Crimping range, max.	300 mm <sup>2</sup>	Crimping range, min.	6 mm <sup>2</sup>
----------------------	---------------------	----------------------	-------------------

## tool data crimping

Crimping type/profile	Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping	Deviation	16 mm
Drive	Electro-hydraulic	Wire end ferrules cross-section, max.	300 mm <sup>2</sup>
Wire end ferrules cross-section, min.	6 mm <sup>2</sup>		

## Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11
ECLASS 14.0	21-04-38-11		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012
RoHS Compliance Status	Compliant

## Approvals

Approvals



ROHS

Conform

## Downloads

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### EPG 60

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## ... for tubular cable lugs

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	ES EPG/HPG 60 WM 150	Version
Order No.	<a href="#">2469620000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483871	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 240	Version
Order No.	<a href="#">2469640000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118484052	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 16	Version
Order No.	<a href="#">2469550000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483833	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 300	Version
Order No.	<a href="#">2469650000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118484045	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 120	Version
Order No.	<a href="#">2469610000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118484007	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 50	Version
Order No.	<a href="#">2469580000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483864	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 25	Version
Order No.	<a href="#">2469560000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483840	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 95	Version
Order No.	<a href="#">2469600000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483895	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 10	Version
Order No.	<a href="#">2469540000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483819	
Qty.	1 pc(s).	

Creation date August 29, 2024 10:56:14 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES EPG/HPG 60 WM 185	Version
Order No.	<a href="#">2469630000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118484038	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 6	Version
Order No.	<a href="#">2469380000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118532937	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 70	Version
Order No.	<a href="#">2469590000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483857	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 WM 35	Version
Order No.	<a href="#">2469570000</a>	Crimping tool insert, WM crimp
GTIN (EAN)	4050118483826	
Qty.	1 pc(s).	

## ... for compression cable lugs

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

## General ordering data

Type	ES EPG/HPG 60 HEX 16	Version
Order No.	<a href="#">2505170000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519549	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 6	Version
Order No.	<a href="#">2505150000</a>	Accessories, Hexagonal crimp
GTIN (EAN)	4050118519532	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 300	Version
Order No.	<a href="#">2505270000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519655	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 185	Version
Order No.	<a href="#">2505250000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519617	
Qty.	1 pc(s).	

Creation date August 29, 2024 10:56:14 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES EPG/HPG 60 HEX 35	Version
Order No.	<a href="#">2505190000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519587	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 50	Version
Order No.	<a href="#">2505200000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519600	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 70	Version
Order No.	<a href="#">2505210000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519594	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 120	Version
Order No.	<a href="#">2505230000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519624	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 25	Version
Order No.	<a href="#">2505180000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519570	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 10	Version
Order No.	<a href="#">2505160000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519556	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 240	Version
Order No.	<a href="#">2505260000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519648	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 150	Version
Order No.	<a href="#">2505240000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519631	
Qty.	1 pc(s).	
Type	ES EPG/HPG 60 HEX 95	Version
Order No.	<a href="#">2505220000</a>	Crimping tool insert, Hexagonal crimp
GTIN (EAN)	4050118519563	
Qty.	1 pc(s).	

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## ... for wire-end ferrules

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	ES EPG 60/HPG AEH 70	Version
Order No.	<a href="#">2577850000</a>	Crimping tool insert
GTIN (EAN)	4050118590692	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG AEH 95	Version
Order No.	<a href="#">2577870000</a>	Crimping tool insert
GTIN (EAN)	4050118590685	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG AEH 120	Version
Order No.	<a href="#">2577880000</a>	Crimping tool insert
GTIN (EAN)	4050118590678	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG AEH 25	Version
Order No.	<a href="#">2577810000</a>	Crimping tool insert
GTIN (EAN)	4050118590722	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG AEH 50	Version
Order No.	<a href="#">2577830000</a>	Crimping tool insert
GTIN (EAN)	4050118590708	
Qty.	1 pc(s).	

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	LADEGERAET EPG
Order No.	<a href="#">1509370000</a>
GTIN (EAN)	4050118318630
Qty.	1 pc(s).

Type	AKKU LI 18B2
Order No.	<a href="#">2858730000</a>
GTIN (EAN)	4064675566137
Qty.	1 pc(s).

Type	AKKU LI 18B5
Order No.	<a href="#">2860070000</a>
GTIN (EAN)	4064675574750
Qty.	1 pc(s).

**... for crimp cable lugs****Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	ES EPG/HPG 60 DIN 6	Version
Order No.	<a href="#">2505280000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519662	
Qty.	1 pc(s).	

## EPG 60

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES EPG 60/HPG DIN 70	Version
Order No.	<a href="#">2505340000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519716	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 95	Version
Order No.	<a href="#">2505350000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519730	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 16	Version
Order No.	<a href="#">2505300000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519709	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 50	Version
Order No.	<a href="#">2505330000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519686	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 10	Version
Order No.	<a href="#">2505290000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519723	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 35	Version
Order No.	<a href="#">2505320000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519679	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 120	Version
Order No.	<a href="#">2505360000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519747	
Qty.	1 pc(s).	
Type	ES EPG 60/HPG DIN 25	Version
Order No.	<a href="#">2505310000</a>	Crimping tool insert, Indent crimp
GTIN (EAN)	4050118519693	
Qty.	1 pc(s).	