

HPG 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Order No.	2453820000
Type	HPG 60
GTIN (EAN)	4050118468427
Qty.	1 pc(s).

HPG 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	285 mm	Depth (inches)	11.22 inch
Height	120 mm	Height (inches)	4.724 inch
Width	500 mm	Width (inches)	19.685 inch
Length	850 mm	Length (inches)	33.465 inch
Net weight	6,434 g		

Technical data

Description of article	Crimping tool 6 - 300 mm ²		
Pressing force	nominal	60 kN	

Description of contact

Crimping range, max.	300 mm ²	Crimping range, min.	6 mm ²
----------------------	---------------------	----------------------	-------------------

tool data crimping

Crimping type/profile	Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping	Drive	Manual - hydraulic
-----------------------	---	-------	--------------------

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
RoHS Compliance Status	Not affected

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format