

PRO COM CAN OPEN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

General ordering data

General ordering data	
Version	Communication module
Order No.	2467320000
Type	PRO COM CAN OPEN
GTIN (EAN)	4050118482225
Qty.	1 pc(s).

PRO COM CAN OPEN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.323 inch
Height	74.4 mm	Height (inches)	2.929 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	75 g		

Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

General data

MTTF	According to Standard	SN 29500
	Operating time (hours), min.	4,082,000 h
	Ambient temperature	40 °C
	Duty cycle	100 %
Protection degree	IP20	
Weight	36 g	

Approbations

Certificate no. (cULus)	E258476	Certificate no. (cULusEX)	E470829
Institute (cULus)	CULUS	Institute (cULusEX)	CULUSEX

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-04-07-92
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-24-26-08	ECLASS 13.0	27-24-26-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1df9fee4-69cb-4b0a-a401-554c8cdbf60e

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

Creation date June 4, 2024 7:30:17 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

PRO COM CAN OPEN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

[Quick start guide – IOT-GW30: CANopen communication with PROtop](#)

[Combinability of PRO COM](#)

Product Change Notification

[PRO COM CAN OPEN Release Notes](#)

Software

[Device description – EDS File](#)

User Documentation

[Operating instruction](#)

Catalogues

[Catalogues in PDF-format](#)

PRO COM CAN OPEN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cable**

Adapter cable from SUB-D to RJ45 for the PRO COM CAN OPEN communication module.

**General ordering data**

Type	PRO CAB SUBD-RJ45 0.5M	Version
Order No.	2578530000	, Sub-D socket 9 poles, RJ45 IP 20, 0.5 m
GTIN (EAN)	4050118589597	
Qty.	1 pc(s).	
Type	PRO CAB SUBD-RJ45 1.0M	Version
Order No.	2578550000	, Sub-D socket 9 poles, RJ45 IP 20, 1 m
GTIN (EAN)	4050118589702	
Qty.	1 pc(s).	
Type	PRO CAB SUBD-RJ45 2.5M	Version
Order No.	2578560000	, Sub-D socket 9 poles, RJ45 IP 20, 2.5 m
GTIN (EAN)	4050118589573	
Qty.	1 pc(s).	