

**FAD BLK4 2XSL20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

**General ordering data**

Order No.	<a href="#">2494590000</a>
Type	FAD BLK4 2XSL20
GTIN (EAN)	8430243373029
Qty.	1 pc(s).

## FAD BLK4 2XSL20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	24 mm	Depth (inches)	0.945 inch
Height	218 mm	Height (inches)	8.583 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	237.908 g		

## Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

## Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

## Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	3 A
Max. current per byte	2 A	Total operating current	6 A

## Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	50 V AC / 71 V DC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.56 kV		

## Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	348848c5-21ff-4d79-b541-7c34c4908172

## Approvals

Approvals



## Downloads

Catalogues [Catalogues in PDF-format](#)

FAD BLK4 2XSL20

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

