

**HDC 10B TSBO 1M20G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

**General ordering data**

Version	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), IP68 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on upper side, Standard, Size of cable entries: M 20
Order No.	<a href="#">2498220000</a>
Type	HDC 10B TSBO 1M20G
GTIN (EAN)	4050118514049
Qty.	1 pc(s).

Creation date August 29, 2024 5:32:54 AM CEST

## HDC 10B TSBO 1M20G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	73 mm	Depth (inches)	2.874 inch
Height	52 mm	Height (inches)	2.047 inch
Width	43 mm	Width (inches)	1.693 inch
Net weight	214 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## Dimensions

Cable entry	w. thread
-------------	-----------

## General data

EMC housings	No	Housing main material	diecast aluminium
Protection degree	IP65 (in plugged condition), IP68 (in plugged condition)	Surface finish	Powder coating

## Version

BG	4	Cable entry	w. thread
Colour (RAL)	RAL 7035	Design	Standard
Design of housing	Cable entry from side, Plug housing	Design of locking system	Side-locking clamp on upper side
Internal thread	M 20	Number of cable entry on top	0
Number of cable entry sideways	1	Size	4
Size of cable entries	M 20	Top part/bottom part/lid	upper part

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02
ECLASS 14.0	27-44-02-02		

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant
Substance	Hydraulic oil

## HDC 10B TSBO 1M20G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@580fc89b de.myview.objectmodel.impl.BlockImpl@318a16a6 de.myview.objectmodel.impl.BlockImpl@666e2a1b de.myview.objectmodel.impl.BlockImpl@26398130 de.myview.objectmodel.impl.BlockImpl@54de7c de.myview.objectmodel.impl.BlockImpl@618ac7f6 de.myview.objectmodel.impl.BlockImpl@76a3172e de.myview.objectmodel.impl.BlockImpl@1c7938cb de.myview.objectmodel.impl.BlockImpl@3a78a206 de.myview.objectmodel.impl.BlockImpl@d7a77c8 de.myview.objectmodel.impl.BlockImpl@638e0b2e de.myview.objectmodel.impl.BlockImpl@36e4c8f4 de.myview.objectmodel.impl.BlockImpl@49f334bc
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6bl

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**HDC 10B TSBO 1M20G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

Type	HDC 10B DMDQ 4BO	Version
Order No.	<a href="#">1665250000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cover for upper part of housing, Side-locking clamp on upper side, Standard
GTIN (EAN)	4008190421953	
Qty.	1 pc(s).	