

IE-FCI-PWB-IND**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert Power large, Type D, Socket connector, IN
Order No.	2500710000
Type	IE-FCI-PWB-IND
GTIN (EAN)	4050118526745
Qty.	1 pc(s).

IE-FCI-PWB-IND

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	42 g
------------	------

Temperatures

Operating temperature	-5 °C...40 °C
-----------------------	---------------

General data

Connector face	Type D	Fire load	770 kJ
Insert type	Insert Power large	Protection degree	IP20

Clampable conductors

Conductor connection cross-section, extremely flexible with wire end ferrule	max.	2.5 mm ²
	min.	1.5 mm ²

Conductor connection cross-section, extremely flexible with wire end ferrule	1.5 ... 2.5 mm ²
--	-----------------------------

Conductor connection cross-section, extremely flexible without wire end ferrule	...
---	-----

Conductor connection cross-section, flexible with wire end ferrule	1.5 ... 2.5 mm ²
--	-----------------------------

Conductor connection cross-section, flexible with wire end ferrule	max.	2.5 mm ²
	min.	1.5 mm ²

Conductor connection cross-section, flexible without wire end ferrule	...
---	-----

Conductor connection cross-section, rigid	min.	1.5 mm ²
	max.	4 mm ²

Conductor connection cross-section, rigid	1.5 ... 4 mm ²
---	---------------------------

Stripping length	9 mm
------------------	------

Type of connection	Screw connection
--------------------	------------------

Technical data

Housing main material	Polycarbonate PC	Rated current	5 A
Rated voltage (AC)	250 V		

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-18-90-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

Approvals

ROHS	Conform
------	---------

IE-FCI-PWB-IND

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Socket Insert Overview EN Socket Insert Overview DE Designation key / Type key
Catalogues	Catalogues in PDF-format


IE-FCI-PWB-IND

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing



IE-FCI-PWB-IND

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Rail adaptor for socket inserts



At Weidmüller you can get everything you need from one source - including accessories for Industrial Ethernet.

The benefits for you:

- tools
- testing instruments
- cable bushings
- cabinet connections
- markers
- dust protection
- power packs
- overvoltage protection

General ordering data

Type	IE-DINRAIL-AD-PWB
Order No.	2534680000
GTIN (EAN)	4050118546354
Qty.	1 pc(s).