

**WPDPC X32 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

|            |  |
|------------|--|
| Version    | Terminal cover, Light Grey, Height: 26.03 mm, Width: 30.1 mm, Depth: 72.1 mm |
| Order No.  | <a href="#">2503380000</a>   |
| Type       | WPDPC X32 GY   |
| GTIN (EAN) | 4050118533347  |
| Qty.       | 12 pc(s).  |

**WPDPC X32 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 72.1 mm  | Depth (inches)  | 2.839 inch |
| Height     | 26.03 mm | Height (inches) | 1.025 inch |
| Width      | 30.1 mm  | Width (inches)  | 1.185 inch |
| Net weight | 4.103 g  |                 |            |

**Material data**

|        |            |                           |     |
|--------|------------|---------------------------|-----|
| Colour | Light Grey | UL 94 flammability rating | V-0 |
|--------|------------|---------------------------|-----|

**System specifications**

|                          |    |                                   |    |
|--------------------------|----|-----------------------------------|----|
| End cover plate required | No | Levels cross-connected internally | No |
|--------------------------|----|-----------------------------------|----|

**Additional technical data**

|                          |    |
|--------------------------|----|
| Explosion-tested version | No |
|--------------------------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ECLASS 9.0  | 27-14-11-92 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                              |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>              |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                     |