

HSS-HF 2.4-4,8 EL SW30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 2.4 - 4.8 mm, black
Order No.	2518930000
Type	HSS-HF 2.4-4,8 EL SW30M
GTIN (EAN)	4050118531138
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

HSS-HF 2.4-4,8 EL SW30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.9 mm	Depth (inches)	0.035 inch
Width	7.6 mm	Width (inches)	0.299 inch
Length	30,000 mm	Length (inches)	1,181.1 inch
Net weight	290 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	black	Halogen	No
Length	30,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	7.6 mm		

Conductor and cable markers

Conductor O.D.	2.4 - 4.8 mm	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	2.4 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 4 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Important note

Product information	External roll holder 1302920000 necessary
---------------------	-------------------------------------------

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity [NFX 70-100-1 2006 + NF X 70-100-2 2006](#)
[BS EN ISO 4589-2 1999](#)
[EN 45545-2:2020](#)

Catalogues [Catalogues in PDF-format](#)

HSS-HF 2.4-4,8 EL SW30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

