

H0,34/12S TK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, Turquoise
Order No.	2525190000
Type	H0,34/12S TK
GTIN (EAN)	4050118536843
Qty.	500 pc(s).

H0,34/12S TK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	125 mm	Height (inches)	4.921 inch
Net weight	0.048 g		

Technical data

Version	Standard
---------	----------

Wire-end ferrules

Conductor cross-section	0.34 mm ²	Contact surface length (L2)	8 mm
L1 in mm	12 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 22		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--