

SAIBC-M-5S-M12-L-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12 socket
Order No.	2525620000
Type	SAIBC-M-5S-M12-L-COD
GTIN (EAN)	4050118536935
Qty.	1 pc(s).

SAIBC-M-5S-M12-L-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	39 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	5.8... 13.5 mm	Cable diameter, max.	13.5 mm
Cable diameter, min.	5.8 mm	Coding	L-coded
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Connection cross-section, max.	1.5 mm ²	Connection cross-section, min.	0.75 mm ²
Contact material	Cu	Contact surface	Gold-plated
Housing main material	Zinc diecast	Number of poles	5
Plugging cycles	500	Pollution severity	3
Protection degree	IP67, when screwed in	Rated current	16 A
Rated current	16 A	Rated voltage	63 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Crimp connection

General Info

Number of poles	5	Connection 1	M12
Connection 2	Crimp	Housing main material	Zinc diecast
Connection thread	M12 socket	Contact material	Cu
Contact surface	Gold-plated	Protection degree	IP67, when screwed in
Plugging cycles	500		

Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Important note

Product information	Enclosures, inserts and crimp contacts need to be ordered separately. 4 x Crimp contact, Socket / 1 x Crimp contact, Pin (FE) for FE-Function.
---------------------	---

SAIBC-M-5S-M12-L-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format


SAIBC-M-5S-M12-L-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme



SAIBC-M-5S-M12-L-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Contacts



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAI-M12L-KBC-1.5	Version
Order No.	2531010000	Crimp contact, Socket connector
GTIN (EAN)	4050118541120	
Qty.	50 pc(s).	
Type	SAI-M12L-KBC-0.75	Version
Order No.	2531000000	Crimp contact, Socket connector
GTIN (EAN)	4050118541113	
Qty.	50 pc(s).	
Type	SAI-M12L-KBC-0.5	Version
Order No.	2530990000	Crimp contact, Socket connector
GTIN (EAN)	4050118541106	
Qty.	50 pc(s).	
Type	SAI-M12L-KBC-2.5	Version
Order No.	2525650000	Crimp contact, Socket connector
GTIN (EAN)	4050118537000	
Qty.	50 pc(s).	

Contacts



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAI-M12L-KSC-2.5FE	Version
Order No.	2525660000	Crimp contact, Pin
GTIN (EAN)	4050118537017	
Qty.	50 pc(s).	
Type	SAI-M12L-KSC-0.75FE	Version
Order No.	2530970000	Crimp contact, Pin
GTIN (EAN)	4050118541083	
Qty.	50 pc(s).	

SAIBC-M-5S-M12-L-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	SAI-M12L-KSC-1.5FE	Version
Order No.	2530980000	Crimp contact, Pin
GTIN (EAN)	4050118541090	
Qty.	50 pc(s).	
Type	SAI-M12L-KSC-0.5FE	Version
Order No.	2530960000	Crimp contact, Pin
GTIN (EAN)	4050118541076	
Qty.	50 pc(s).	