

**HS-HF 1.2-2.4/12 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | Conductor and cable markers, 1.2 - 2.4 mm, 12.7 x 5 mm, white |
| Order No.          | <a href="#">2526230000</a>                                    |
| Type               | HS-HF 1.2-2.4/12 MM W   |
| GTIN (EAN)         | 4050118537383   |
| Qty.               | 4,000 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>         |

## HS-HF 1.2-2.4/12 MM W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 12.7 mm | Height (inches) | 0.5 inch   |
| Width      | 5 mm    | Width (inches)  | 0.197 inch |
| Net weight | 0.127 g |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

### General data

|                                   |              |                                   |        |
|-----------------------------------|--------------|-----------------------------------|--------|
| Colour                            | white        | Halogen                           | No     |
| Material                          | Polyolefine  | Number per roll                   | 4,000  |
| Operating temperature range       | -55...105 °C | Operating temperature range, max. | 105 °C |
| Operating temperature range, min. | -55 °C       | Width                             | 5 mm   |

### Conductor and cable markers

|                                   |                      |                                  |                            |
|-----------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D.                    | 1.2 - 2.4 mm         | Conductor O.D., max.             | 2.4 mm                     |
| Conductor O.D., min.              | 1.2 mm               | Conductor cross-section, max.    | 0.5 mm <sup>2</sup>        |
| Conductor cross-section, min.     | 0.25 mm <sup>2</sup> | Cross-section for connected wire | 0.25 - 0.5 mm <sup>2</sup> |
| Halogen                           | No                   | Rate of shrinkage                | 2:1                        |
| Recommended shrinking temperature | 90 °C                |                                  |                            |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |
| ECLASS 14.0 | 27-28-11-02 |             |             |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN ISO 4589-2 1999</a><br><a href="#">EN 45545-2:2020</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |

**HS-HF 1.2-2.4/12 MM W**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**HS-HF 1.2-2.4/12 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM-HS 60/300 SW     | Version    |
| Order No.  | <a href="#">2448880000</a> | Ink ribbon |
| GTIN (EAN) | 4050118462944              |            |
| Qty.       | 1 pc(s).                   |            |

**THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | MM PLUS ROLLER 110         |
| Order No.  | <a href="#">2672590000</a> |
| GTIN (EAN) | 4050118708097              |
| Qty.       | 1 pc(s).                   |

**HS-HF 1.2-2.4/12 MM W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | THM MMP ROLLER 115         |
| Order No.  | <a href="#">1357420000</a> |
| GTIN (EAN) | 4050118160314              |
| Qty.       | 1 pc(s).                   |