

HS-HF 4.8-9.5/12 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 4.8 - 9.5 mm, 12.7 x 16.1 mm, white
Order No.	2526310000
Type	HS-HF 4.8-9.5/12 MM W
GTIN (EAN)	4050118537468
Qty.	2,000 pc(s).
compatible printer	2599430000 2599440000

HS-HF 4.8-9.5/12 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.03 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	16.1 mm	Width (inches)	0.634 inch
Net weight	0.365 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	white	Halogen	No
Material	Polyolefine	Number per roll	2,000
Operating temperature range	-55...105 °C	Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C	Width	16.1 mm

Conductor and cable markers

Conductor O.D.	4.8 - 9.5 mm	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	4.8 mm	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	4 mm ²	Cross-section for connected wire	4 - 16 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020
Catalogues	Catalogues in PDF-format

HS-HF 4.8-9.5/12 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HS-HF 4.8-9.5/12 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version
Order No.	2448880000	Ink ribbon
GTIN (EAN)	4050118462944	
Qty.	1 pc(s).	

THM MULTIMARK

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP ROLLER 115
Order No.	1357420000
GTIN (EAN)	4050118160314
Qty.	1 pc(s).

HS-HF 4.8-9.5/12 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MM PLUS ROLLER 110
Order No.	2672590000
GTIN (EAN)	4050118708097
Qty.	1 pc(s).