

HDC XX6A03 MFSXXXX-3000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	
Order No.	2548113000
Type	HDC XX6A03 MFSXXXX-3000
GTIN (EAN)	4050118557350
Qty.	1 pc(s).

HDC XX6A03 MFSXXXX-3000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.001 g
------------	---------

Temperatures

Limit temperature	-30 °C ... 90 °C
-------------------	------------------

General data

Cable length	30 m	Category	Cat. 6A
Coding	X-coded	Contact surface	Au (Gold)
Insulation strength	≥ 1000 MΩ	Module side version	Male
Number of poles	8	Opposite side version	Female
Plugging cycles	≥ 100	Pollution severity	2
Rated current	0.5 A	Rated voltage	50 V
Transmission rate	10 Gbit/s		

Cable technical specifications

Cable length	30 m
Colour coding	white / blue, white / orange, white / green, white / brown
Halogen	halogen-free
Insulation	Polyolefin
Outside diameter	Diameter 8.9 mm
Outside diameter	8.9 mm
Sheath material	PUR
Sheathing colour	green (RAL 6018)
Shielded	Yes

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-07	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-07	ECLASS 11.0	27-06-03-07
ECLASS 12.0	27-06-03-07	ECLASS 13.0	27-06-03-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format