

**WQB 4 WTL 6/4 FF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 4, Pitch in mm (P): 11.10, Insu- lated: Yes, 41 A, orange
Order No.	<a href="#">2550750000</a>
Type	WQB 4 WTL 6/4 FF
GTIN (EAN)	4050118560619
Qty.	10 pc(s).

## WQB 4 WTL 6/4 FF

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	29.32 mm	Height (inches)	1.154 inch
Width	40.4 mm	Width (inches)	1.591 inch
Net weight	4.2 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Wemid	Colour	orange
----------	-------	--------	--------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

## Dimensions

Pitch in mm (P)	11.1 mm
-----------------	---------

## General

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

## Rating data

Rated current	41 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Approvals

ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>