

WQB 7 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 7, Pitch in mm (P): 11.10, Insu- lated: Yes, 41 A, orange
Order No.	2550770000
Type	WQB 7 WTL 6/4 FF
GTIN (EAN)	4050118560633
Qty.	10 pc(s).

WQB 7 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	29.32 mm	Height (inches)	1.154 inch
Width	73.7 mm	Width (inches)	2.902 inch
Net weight	15.4 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Wemid	Colour	orange
----------	-------	--------	--------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	11.1 mm
-----------------	---------

General

Installation advice	Direct mounting	Number of poles	7
---------------------	-----------------	-----------------	---

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Creation date July 2, 2024 10:03:30 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.