

WQB 10 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, orange, 41 A, Number of poles: 10, Pitch in mm (P): 11.10, Insulated: Yes, Width: 106.9 mm
Order No.	2550780000
Type	WQB 10 WTL 6/4 FF
GTIN (EAN)	4050118560640
Qty.	10 pc(s).

WQB 10 WTL 6/4 FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	29.32 mm	Height (inches)	1.154 inch
Width	106.9 mm	Width (inches)	4.209 inch
Net weight	22.6 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Wemid	Colour	orange
----------	-------	--------	--------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	11.1 mm
-----------------	---------

General

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

WQB 10 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)