

CD-RET 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

| | |
|------------|----------------------------|
| Version | Cable duct binder |
| Order No. | 2554030000 |
| Type | CD-RET 60 |
| GTIN (EAN) | 4050118564167 |
| Qty. | 500 pc(s). |

CD-RET 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|-----|
| Net weight | 2 g |
|------------|-----|

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General information

| | |
|-----------------------------|--------------------------------|
| Channel width | 37.5/50/60 |
| Material | Polyamide 6 (PA 6) |
| Operating temperature range | -40...100 °C |
| Usage | For 40/ 50/ 60 mm wiring ducts |

| | |
|---------------------------|--------|
| Colour | yellow |
| Non-tracking | Yes |
| UL 94 flammability rating | HB |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001018 | ETIM 7.0 | EC001018 |
| ETIM 8.0 | EC001018 | ETIM 9.0 | EC001018 |
| ECLASS 9.0 | 27-40-07-65 | ECLASS 9.1 | 27-40-07-65 |
| ECLASS 10.0 | 27-40-07-65 | ECLASS 11.0 | 27-40-07-65 |
| ECLASS 12.0 | 27-40-07-65 | ECLASS 13.0 | 27-40-07-65 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|