

FF-FIMT 2X 55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Version	Filter mat, IP55, white
Order No.	2556670000
Type	FF-FIMT 2X 55
GTIN (EAN)	4050118567298
Qty.	5 pc(s).

FF-FIMT 2X 55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	108 mm	Height (inches)	4.252 inch
Width	116 mm	Width (inches)	4.567 inch
Net weight	12.4 g		

Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

General data

Colour	white	Filter class	G 4
Operating temperature range	-40...55 °C	Protection class (UL)	Type 12
Type of mounting	Snap-on	With filter	Yes

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
ETIM 8.0	EC002513	ETIM 9.0	EC002513
ECLASS 9.1	27-18-07-06	ECLASS 10.0	27-18-07-06
ECLASS 11.0	27-18-07-06	ECLASS 12.0	27-18-07-06
ECLASS 13.0	27-18-07-06		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format