

**FF 32 55/230V GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

**General ordering data**

Version	Filter fan, IP55, grey
Order No.	<a href="#">2556700000</a>
Type	FF 32 55/230V GY
GTIN (EAN)	4050118567328
Qty.	1 pc(s).

## FF 32 55/230V GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	93 mm	Depth (inches)	3.661 inch
Height	202 mm	Height (inches)	7.953 inch
Width	202 mm	Width (inches)	7.953 inch
Net weight	870 g		

## Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

## General data

Colour	grey		
Current consumption	Mains frequency	50 Hz	
	Current	0.12 A	
	Mains frequency	60 Hz	
	Current	0.18 A	
EMC version	No		
Fan type	Roof fan		
Filter class	G 4		
Fuse	6 A		
Height of installation cut-outs	177 mm		
MTBF	37,500 h		
Mounting depth	87 mm		
Mounting height	6 mm		
Noise emission	40 dB(A)		
Operating temperature range	-40...55 °C		
Power	Mains frequency	50 Hz	
	nominal	19 W	
	Mains frequency	60 Hz	
	nominal	18 W	
Protection class (UL)	Type 12		
Rated AC voltage	230 V		
Rated voltage	230 V AC $\pm$ 10%		
Size	3		
Type of connection	Terminal strip		
Type of mounting	Snap-on		
UL 94 flammability rating	V-0		
UV-resistant	Yes		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	55 m³/h	
	Exhaust filter	IP55	
	Mains frequency	60 Hz	
	Volume flow	64 m³/h	
	Exhaust filter	IP55	
Volume flow, free-blowing	Mains frequency	50 Hz	
	Volume flow	100 m³/h	
	Mains frequency	60 Hz	
	Volume flow	110 m³/h	
Volume flow, free-blowing at 50 Hz	100 m³/h		
Volume flow, free-blowing at 60 Hz	110 m³/h		
Width of installation cut-outs	177 mm		
With filter	Yes		
With protective cover	Yes		

Creation date May 23, 2024 3:53:25 AM CEST

**FF 32 55/230V GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ECLASS 9.1	27-18-07-16	ECLASS 10.0	27-18-07-16
ECLASS 11.0	27-18-07-16	ECLASS 12.0	27-18-07-16
ECLASS 13.0	27-18-07-16		

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E252704

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Installation- and operating instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


## FF 32 55/230V GY

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Graph



## Graph



## FF 32 55/230V GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Filter fan



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

## General ordering data

Type	FF-FIMT 3X 54	Version
Order No.	<a href="#">2556720000</a>	Filter mat, IP54, white
GTIN (EAN)	4050118567342	
Qty.	5 pc(s).	
Type	FF-FIMT 3X 55	Version
Order No.	<a href="#">2556730000</a>	Filter mat, IP55, white
GTIN (EAN)	4050118567359	
Qty.	5 pc(s).	

## Exhaust filter



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

## General ordering data

Type	EF 30 54 BK	Version
Order No.	<a href="#">2557140000</a>	Exhaust filter, IP54, black
GTIN (EAN)	4050118567779	
Qty.	1 pc(s).	
Type	EF 30 55 GY	Version
Order No.	<a href="#">2557150000</a>	Exhaust filter, IP55, grey
GTIN (EAN)	4050118567786	
Qty.	1 pc(s).	
Type	EF 30 54 GY	Version
Order No.	<a href="#">2557130000</a>	Exhaust filter, IP54, grey
GTIN (EAN)	4050118567762	
Qty.	1 pc(s).	
Type	EF 30 55 BK	Version
Order No.	<a href="#">2557160000</a>	Exhaust filter, IP55, black
GTIN (EAN)	4050118567793	
Qty.	1 pc(s).	