

FF-EMC 65 55/230V GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

For use near electromagnetic fields. Secure contact surface without the need for a beryllium copper seal and particularly environmentally friendly as no metal reinforced plastics are required.

General ordering data

Version	Filter fan, IP55, grey
Order No.	2557450000
Type	FF-EMC 65 55/230V GY
GTIN (EAN)	4050118568080
Qty.	1 pc(s).
Available until	2023-11-10

FF-EMC 65 55/230V GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	157 mm	Depth (inches)	6.181 inch
Height	320 mm	Height (inches)	12.598 inch
Width	320 mm	Width (inches)	12.598 inch
Net weight	3,280 g		

Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

General data

Colour	grey		
Current consumption	Mains frequency	50 Hz	
	Current	0.35 A	
	Mains frequency	60 Hz	
	Current	0.45 A	
EMC version	EN 61000-3-2,-3, EN 61000-6-2, 3		
Fan type	Shelf		
Filter class	G 4		
Fuse	6 A		
Height of installation cut-outs	292 mm		
MTBF	40,000 h		
Mounting depth	150 mm		
Mounting height	7 mm		
Noise emission	54 dB(A)		
Operating temperature range	-40...55 °C		
Power	Mains frequency	50 Hz	
	nominal	80 W	
	Mains frequency	60 Hz	
	nominal	100 W	
Protection class (UL)	Type 12		
Rated AC voltage	230 V		
Rated voltage	230 V AC \pm 10%		
Size	6		
Type of connection	Spring contact		
Type of mounting	Snap-on		
UL 94 flammability rating	V-0		
UV-resistant	Yes		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	380 m³/h	
	Exhaust filter	IP55	
	Mains frequency	60 Hz	
	Volume flow	380 m³/h	
	Exhaust filter	IP55	
Volume flow, free-blowing	Mains frequency	50 Hz	
	Volume flow	505 m³/h	
	Mains frequency	60 Hz	
	Volume flow	505 m³/h	
Volume flow, free-blowing at 50 Hz	505 m³/h		
Volume flow, free-blowing at 60 Hz	505 m³/h		
Width of installation cut-outs	292 mm		
With filter	Yes		

FF-EMC 65 55/230V GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ECLASS 9.1	27-18-07-16	ECLASS 10.0	27-18-07-16
ECLASS 11.0	27-18-07-16	ECLASS 12.0	27-18-07-16
ECLASS 13.0	27-18-07-16		

Approvals

ROHS	Conform
------	---------




Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Installation- and operating instructions
Catalogues	Catalogues in PDF-format

FF-EMC 65 55/230V GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Graph****Shielding effectiveness measurements****Graph****Graph**

FF-EMC 65 55/230V GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Filter fan



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Type	FF-FIMT 6X 54	Version
Order No.	2567310000	Filter mat, IP54, white
GTIN (EAN)	4050118576955	
Qty.	5 pc(s).	
Type	FF-FIMT 6X 55	Version
Order No.	2557050000	Filter mat, IP55, white
GTIN (EAN)	4050118567687	
Qty.	5 pc(s).	

Exhaust filter



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	EF-EMC 60 55 GY	Version
Order No.	2557710000	Exhaust filter, IP55, grey
GTIN (EAN)	4050118568356	
Qty.	1 pc(s).	
Type	EF-EMC 60 54 BK	Version
Order No.	2557700000	Exhaust filter, IP54, black
GTIN (EAN)	4050118568349	
Qty.	1 pc(s).	
Type	EF-EMC 60 55 BK	Version
Order No.	2557720000	Exhaust filter, IP55, black
GTIN (EAN)	4050118568363	
Qty.	1 pc(s).	
Type	EF-EMC 60 54 GY	Version
Order No.	2557690000	Exhaust filter, IP54, grey
GTIN (EAN)	4050118568332	
Qty.	1 pc(s).	