

CD-FLEX 12.5X12.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Flexible wiring duct, 12.5 mm x 12.5 mm, 5.00 mm x 7.50 mm, 500 mm
Order No.	2562770000
Type	CD-FLEX 12.5X12.5
GTIN (EAN)	4050118571585
Qty.	50 pc(s).

CD-FLEX 12.5X12.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	12.5 mm	Height (inches)	0.492 inch
Width	12.5 mm	Width (inches)	0.492 inch
Length	500 mm	Length (inches)	19.685 inch
Net weight	12 g		

Temperatures

Operating temperature range	-15...80 °C
-----------------------------	-------------

General information

Colour	grey (similar to RAL 7001)	Flexible wiring duct	Yes
Lid	No	Material	Polypropylene
Non-tracking	Yes	Operating temperature range	-15...80 °C
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	With adhesive	UL 94 flammability rating	V-2
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--