

ES EPG 60 ISO 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert
Order No.	2577940000
Type	ES EPG 60 ISO 10
GTIN (EAN)	4050118590647
Qty.	1 pc(s).

ES EPG 60 ISO 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	22 mm	Depth (inches)	0.866 inch
Height	42 mm	Height (inches)	1.654 inch
Width	42 mm	Width (inches)	1.654 inch
Net weight	25 g		

Crimp inserts

Crimp cross-section copper	10	Crimping width	7 mm
Crimping width in mm	7		

Description of contact

Conductor cross-section, max. AWG	8	Type of contact	Insulated connector
-----------------------------------	---	-----------------	---------------------

tool data crimping

Cable lug cross section	nominal	10 mm ²
-------------------------	---------	--------------------

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	/
------------	---

Downloads

Catalogues	Catalogues in PDF-format
------------	--

ES EPG 60 ISO 10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Forked cable lugs

**Insulated forked-cable connector made from PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	KQIG-M6/-10	Version
Order No.	1491340000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118301304	10 mm ²
Qty.	50 pc(s).	
Type	KQIG-M5/-10	Version
Order No.	1491330000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118301335	10 mm ²
Qty.	50 pc(s).	

Crimp cable lugs

**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	KQI-M10/-16	Version
Order No.	1492510000	cable lug, terminal end, Insulated cable connector, 16 mm ² , 16 mm ² -
GTIN (EAN)	4050118302288	16 mm ²
Qty.	50 pc(s).	
Type	KQI-M6/-10	Version
Order No.	1492440000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118302356	10 mm ²
Qty.	50 pc(s).	
Type	KQI-M10/-10	Version
Order No.	1492470000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118302233	10 mm ²
Qty.	50 pc(s).	
Type	KQI-M5/-10	Version
Order No.	1492430000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118302349	10 mm ²
Qty.	50 pc(s).	

ES EPG 60 ISO 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	KQI-M8/-10	Version
Order No.	1492450000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ² -
GTIN (EAN)	4050118302226	10 mm ²
Qty.	50 pc(s).	

Pin cable lugs**Insulated pin-cable connector made from PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	KSI/-10	Version
Order No.	1491430000	cable lug, terminal end, Insulated cable connector, 10 mm ² , 10 mm ²
GTIN (EAN)	4050118301403	
Qty.	50 pc(s).	