

**ES EPG 60 ISO 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Version	Crimping tool insert
Order No.	<a href="#">2577940000</a>
Type	ES EPG 60 ISO 10
GTIN (EAN)	4050118590647
Qty.	1 pc(s).

**ES EPG 60 ISO 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	22 mm	Depth (inches)	0.866 inch
Height	42 mm	Height (inches)	1.654 inch
Width	42 mm	Width (inches)	1.654 inch
Net weight	25 g		

**Crimp inserts**

Crimp cross-section copper	10	Crimping width	7 mm
Crimping width in mm	7		

**Description of contact**

Conductor cross-section, max. AWG	8	Type of contact	Insulated connector
-----------------------------------	---	-----------------	---------------------

**tool data crimping**

Cable lug cross section	nominal	10 mm <sup>2</sup>
-------------------------	---------	--------------------

**Classifications**

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## ES EPG 60 ISO 10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Crimp cable lugs



## Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

## General ordering data

Type	KQI-M10/-16	Version
Order No.	<a href="#">1492510000</a>	cable lug, terminal end, Insulated cable connector, 16 mm <sup>2</sup> , 16 mm <sup>2</sup> -
GTIN (EAN)	4050118302288	16 mm <sup>2</sup>
Qty.	50 pc(s).	
Type	KQI-M5/-10	Version
Order No.	<a href="#">1492430000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118302349	10 mm <sup>2</sup>
Qty.	50 pc(s).	
Type	KQI-M6/-10	Version
Order No.	<a href="#">1492440000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118302356	10 mm <sup>2</sup>
Qty.	50 pc(s).	
Type	KQI-M10/-10	Version
Order No.	<a href="#">1492470000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118302233	10 mm <sup>2</sup>
Qty.	50 pc(s).	
Type	KQI-M8/-10	Version
Order No.	<a href="#">1492450000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118302226	10 mm <sup>2</sup>
Qty.	50 pc(s).	

## Pin cable lugs



## Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	KSI/-10	Version
Order No.	<a href="#">1491430000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup>
GTIN (EAN)	4050118301403	
Qty.	50 pc(s).	

## ES EPG 60 ISO 10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Forked cable lugs

**Insulated forked-cable connector made from PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	KQIG-M6/-10	Version
Order No.	<a href="#">1491340000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118301304	10 mm <sup>2</sup>
Qty.	50 pc(s).	
Type	KQIG-M5/-10	Version
Order No.	<a href="#">1491330000</a>	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> -
GTIN (EAN)	4050118301335	10 mm <sup>2</sup>
Qty.	50 pc(s).	