

ES APG80 WM 400**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	400mm ² , WM crimp
Order No.	2578060000
Type	ES APG80 WM 400
GTIN (EAN)	4064675018124
Qty.	1 pc(s).

ES APG80 WM 400

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	70 g
------------	------

Crimp inserts

Crimp cross-section copper	400	Crimping width	7 mm
Crimping width in mm	7		

Description of contact

Conductor cross-section, max. AWG	750	Crimping range, max.	400 mm ²
-----------------------------------	-----	----------------------	---------------------

tool data crimping

Cable lug cross section	nominal	400 mm ²
Crimping type/profile	WM crimp	

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--